


Moisture analyser KERN MLS-N



Features

- Backlit Grafik display, digit height 14 mm
 - 1 Moisture display in %
 - 2 Current moisture content in %
 - 3 Printer interval 30 sec
 - 4 Printout in moisture %
 - 5 Switch off mode
 - 6 Type of drying *Standard*
 - 7 Previous drying time
 - 8 Status bar
 - 9 Current temperature
 - 10 Type of drying *Standard*
 - 11 Target temperature
 - 12 Drying process active
- 13 Halogen quartz glass heater 400 W
- Internal memory for automatic sequence of 10 drying programs (12 free digits for each memory) and 100 drying processes carried out, which can be recalled individually
- Practical net weighing assistance to a defined target value [g] with adjustable tolerance range 1 - 25 % of the target value
- The last value measured remains on the display until it is replaced by a new measurement
- Simple „step-by-step“ user guidance in the display in the following languages D, GB, F, I, E, PL
- 14 10 sample plates included
- Can be connected to PC keyboard
- Application handbook: On the internet, you will find a practical application handbook containing many examples, field reports, adjustments and tips for each KERN moisture analyser

Moisture analyser with 10 memory possibilities and graphic display

STANDARD

CAL EXT

MEMORY

RS 232

GLP

230 V

FORCE

1 DAY

3 YEARS
WARRANTY

DKD

+3 DAYS

OPTION

DKD































+3 DAYS

KERN	MLS 50-3HA160N
Readout [d]	0,001 g / 0,01 %
Weighing range [Max]	50 g
Reproducibility, weight of sample 2 g	0,5 %
Reproducibility, weight of sample 10 g	0,02 %
Display after drying (Display can be switched over at any time)	
Moisture [%] = Weight loss (WL) from SW (startweight)	0 - 100 %
Dry mass [%] = Residual weight (RW) from SW	100 - 0 %
ATRO [%] [(SG-RG) : RG] · 100%	0 - 999 %
Restgewicht [g]	Absolute value in [g]
Temperature range	50° - 160°C in steps up to 1°C
Drying modes	<ul style="list-style-type: none">• Standard drying• Drying in levels• Gentle drying• Pre-heat level, can be switched on
Switch off criteria	<ul style="list-style-type: none">• When the set time has expired (1 - 9 h 59 min)• When the weight loss per unit of time falls below the target value (both values freely adjustable mg/sec)
Recall of measurement	Interval adjustable from 1 sec - 5 min (only in connection with KERN YKB-01N printer or PC)
Overall dimensions WxDxH	210x335x156 mm
Net weight	approx. 6,3 kg
Option DKD Calibr. Certificate	963-127

Accessories

- 14 Sample plates aluminium, Ø 92 mm. Unit of 80 pieces, KERN MLB-A01
- Roundfi berglass filter e.g. for samples that splash or become encrusted. Unit of 80 pieces, KERN RH-A02
- Temperature calibration set consists of measuring sensor and display device, KERN MLB-A11
- Protective working cover standard, can be reordered, KERN ALS-A02
- Suitable printers see page 130

KERN Pictograms

 Internal adjusting (CAL): Quick setting of the balance's accuracy with internal adjusting weight (motordriven).	 Adjusting program (CAL): For quick setting of the balance's accuracy. External adjusting weight required.	 Memory: Balance contains memories, e.g. for item data, weighing data, tare weights etc. PLU
 Data interface RS-232: To connect the balance to a printer, PC or network	 Control outputs (optocoupler, digital I/O) to connect relays, signal lamps, valves, etc.	 Interface for second balance: for direct connection of a second balance
 Network interface: For connecting the scale to an Ethernet network. With KERN products you can also use a universal RS-232/LAN converter.	 GLP/ISO record keeping: of weighing data with date, time and identification-no. Only with printers from KERN.	 Piece counting: Reference quantities selectable. Display can be switched from piece to weight
 Net-total weighing: weight of tare cup and weight of components memorized in two separate stores.	 Percentage determination: Determining the deviation in % from the target value (100%).	 Weighing units: Can be switched to e. g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details.
 Weighing with tolerance range: Upper and lower limiting can be programmed individually, e.g. dosing/sorting and portioning.	 Vibration-free weighing: (Animal weighing program) Vibrations are filtered out so that a stable weight is obtained.	 Spray and dust protection IPxx: The type of protection is shown by the pictogram. For details see the glossary.
 Stainless steel: the balance is protected against corrosion.	 Suspended weighing: load support with hook on the underside of the balance.	 Battery operation: Ready for battery operation. The battery type is specified for each device.
 Rechargeable battery pack: rechargeable set.	 Mains adapter: 230V/50Hz in standard version for Germany. On request GB, AUS or USA version.	 Power supply: integrated in balance. 230V/50Hz in Germany. More standards e. g. GB, AUS, USA on request.
 Strain gauges: Electrical resistor on an elastic deforming body.	 Tuning fork principle: A resonating body is electromagnetically excited, causing it to oscillate.	 Electromagnetic force compensation: Coil in a permanent magnet. For the most accurate weighings.
 Single cell technology: Advanced version of the force compensation principle with the highest level of precision.	 Verification possible: The time required for verification is specified in the pictogram.	 DKD calibration possible: The time required for DKD calibration is shown in days in the pictogram.
 Package shipment: The time required to manufacture the product internally is shown in days in the pictogram.	 Pallet shipment: The time required to manufacture the product internally is shown in days in the pictogram.	 Warranty: The warranty period is shown in the pictogram.

Precision is our business

To ensure the high level of precision of your balance, KERN offers the appropriate test weight package for your balance. This consists of the test weight, box and DKD calibration certificate, as proof of its accuracy. The best way to ensure proper balance calibration.

In the extensive KERN test weight range, you will find test weights in the international OIML error limit classes: E1, E2, F1, F2, M1, M2, and M3 with weights from 1 mg to 2000 kg.

The KERN DKD calibration laboratory for electronic balances and weights has been accredited by DKD since 1994 and today is one of the most modern and best-equipped DKD calibration laboratories for balances, test weights and force-measurement in Europe.
(DKD = German Calibration Service ~ UKAS)

Your KERN specialist dealer:

Thanks to the high level of automation, we can carry out DKD calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

Range of services:

- DKD calibration of balances with a maximum load of up to 6000 kg
- DKD calibration of weights in the range of 1 mg – 500 kg
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DKD calibration certificates in the following languages
D, GB, F, I, E, NL, PL

Do you have questions about your scale, the corresponding test weight or the calibration service? Your KERN specialist dealer will be pleased to assist you.

KERN – Professional measuring. Measuring technology and testing services from a single source

