

TH15 Pump Head

TH15 pump head can run in reversible direction, the tubing will have longer life if in CW turns; for bigger outlet pressure, please make it turn in CCW direction.

The shell of this pump head is made of PC which is transparent; it is convenient for changing tubing and observing working status. Adopts self-adaptive spring structure as component of rollers

)



Specifications:

- Flow range: $\leq 160\text{mL/min}$
- Speed range: $\leq 100\text{rpm}$
- Shell material: PC
- Roller material: POM
- Roller number: 2
- Gap adjustment: Automatic adjustment
- Applicable tubes: 13#, 14#, 19#, 16#, 25#.

Appearance size

